



Installation Requirements

Übermilk

Benchtop

Minimum Bench-Space Depth 60cm

We suggest an additional 30cm of space be allowed at the front and sides of machine for a comfortable work area.

- Width: 180mm
- Height: 540mm
- Depth: 420mm
- Weight: 25kg

Power

- 15 amp single-phase power-point within 1m of machine (must be dedicated power supply for the Übermilk)

Milk Supply

- The milk supply needs to be under the counter or on top
 - The maximum length of the milk hose from the Übermilk to the milk source is 1.8m
 - The Übermilk is suitable to use with most milk-storage containers.
-

